We connect and protect

Heavy-Duty Pipe Clamp 54-60mm, M8/M10, Electrogalvanized

KATALOGOVÉ ČÍSLO

HDN047EG

VLASTNOSTI

Fillet welded connector nut has flats to accommodate spanners

VLASTNOSTI PRODUKTU

Article Number: 579046
Nut Included: Yes
Materiál: Ocel
Povrchová úprava: Electrogalvanized
Outer Diameter (OD): 54 - 60 mm
Rod Size (RS): M8;M10
Width (W): 25 mm
Thickness (T): 2 mm
Screw Diameter (Sc): 8 mm
Screw Diameter metric (Sc): M8
Screw Length (L): 25mm
Static Load: 2000N

DIAGRAMS





UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.