

FleXbus IP55 Conductor Entry, Double Entry, 126 mm x 157 mm x 175 mm

Data Solutions

KATALOGOVÉ ČÍSLO

FLEXCEIP55C502



nVent ERIFLEX FleXbus IP55 Conductor Entries can be used for switchboard and/or power supply cover to upgrade an installation to IP55 level. Protect the nVent ERIFLEX FleXbus Conductor insulation against sharp edges from power supply or switchboard top cover.

CERTIFICATIONS



VLASTNOSTI

Made with soft PVC to follow any potential conductor bending radius

Sealing around the conductor is made by a self-fusing tape with a strong adhesive

Good resistance to solvent and hydrocarbon splashes

Adaptable to any nVent ERIFLEX FleXbus conductor cross section by cutting the top material with traditional cutter

High acid resistance

UV resistance

RoHS compliant

Flame retardant

VLASTNOSTI PRODUKTU

Article Number: 508142

Materiál: Polyvinylchloride

Enclosure Rating: IP 55

Typ: Double Entry

Working Temperature: -40 to 140°C

A: 126mm

B: 157mm


C: 175mm

Conductor Size: 220 mm²; 360 mm²; 545 mm²; 640 mm²

Torque (TQ): 2.5N·m

Unit Weight: 0.8kg

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE