

# Neutral Bar for TD Distribution Blocks, 125 A IEC

## Data Solutions

### KATALOGOVÉ ČÍSLO

---

**NB-125A**



### CERTIFICATIONS

---



### VLASTNOSTI

---

Attaches to four pole distribution blocks for increased wire capacity

Direct electrical connection

Strong mechanical assembly

Transparent protection cover

Halogen free

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

### VLASTNOSTI PRODUKTU

---

Article Number: 563841

Max Current Rating, IEC: 125A

Short Term Withstand Current (Icw) 1s: 4.5kA

Peak Short Circuit Current (Ipk): 30kA

Line Side Number of Connections: 3

Line Side Compact Stranded Wire Size: 10 - 25 mm<sup>2</sup>

Line Side Stranded Wire Size - Ferrule: 6 – 16mm<sup>2</sup>

Load Side Number of Connections: 9

Load Side Compact Stranded Wire Size: 2,5 - 6 mm<sup>2</sup>

Load Side Stranded Wire Size - Ferrule: 1,5 – 6 mm<sup>2</sup>

Hloubka (D): 37.4mm

Height (H): 34.3mm

Width (W): 142mm

Unit Weight: 0.17kg


For Use With: TD-100-125AL (563830); TD-100-125ALL (563840)

Flammability Rating: UL® 94V-0

Complies With: IEC® 60947-7-1

## DIAGRAMS

---



## UPOZORNĚNÍ

---

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**