

Neutral Bar for TD Distribution Blocks, 160 A IEC

Data Solutions

KATALOGOVÉ ČÍSLO

NB-160A



CERTIFICATIONS



VLASTNOSTI

Attaches to four pole distribution blocks for increased wire capacity

Direct electrical connection

Strong mechanical assembly

Transparent protection cover

Halogen free

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

VLASTNOSTI PRODUKTU

Article Number: 563201

Max Current Rating, IEC: 160A

Short Term Withstand Current (Icw) 1s: 6.2kA

Peak Short Circuit Current (Ipk): 35kA

Line Side Number of Connections: 4

Line Side Compact Stranded Wire Size: 10 - 35 mm²

Line Side Stranded Wire Size - Ferrule: 10 – 25mm²

Load Side Number of Connections: 10

Load Side Compact Stranded Wire Size: 2,5 - 16 mm²

Load Side Stranded Wire Size - Ferrule: 1,5 – 16 mm²

Hloubka (D): 41.4mm

Height (H): 34.3mm

Width (W): 170mm


Unit Weight: 0.2kg

For Use With: TD-160A (563200); TD-160AL (563990)

Flammability Rating: UL® 94V-0

Complies With: IEC® 60947-7-1

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE