

Flat Braided Power Shunt, 1,000 mm², 450 mm

Data Solutions

KATALOGOVÉ ČÍSLO

PBC1000X450



CERTIFICATIONS



VLASTNOSTI

Ideal for transformer-busduct link

Solid palms can be drilled to fit customer specific designs

Extra flexible power connection and good resistance to vibration

VLASTNOSTI PRODUKTU

Article Number: 564900

Materiál: Copper

Povrchová úprava: Tinned

Wire Diameter: 0.15mm

Cross Section: 1000mm²

ΔT 30 K: 1651A

ΔT 50 K: 2188A

Length (L): 450mm

A: 105mm

B: 100mm

C: 16mm

2 Bar Current Coefficient: 1.6

Unit Weight: 5.47kg

DALŠÍ PODROBNOSTI O PRODUKTU

When used in parallel, the two shunts must be spaced with a minimum distance equal to the thickness of the shunt to allow air cooling.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE