

Outdoor Modular 24 U 1330H 900W 600D

Data Solutions

KATALOGOVÉ ČÍSLO

10149-573



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

VLASTNOSTI

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from front, all sides possible upon request

100 mm high plinth, 200 and 300 mm possible

Top cover with louvers, can be upgraded with fans or A/C unit

RAL 7035 powder coating, other colors available upon request

VLASTNOSTI PRODUKTU

Product Type: Outdoor Cabinet

Produktová řada: Modular

Rack Height: 24U

Výška: 1330mm

Šířka: 900mm

Hloubka: 600mm

Wall Type: Double Walled

Door Type: Plain; Double Door

Cooling: Passive

EMC Shielding: Optional

Množství v balení: 1

Battery Compartment: Optional

Burglar Resistance: Optional

Povrchová úprava: Strukturovaný Práškový

Frame Material: Hliník

Materiál: Hliník; Ocel

Plinth Height: 100mm

Mounting Setup: Optional

DALŠÍ PODROBNOSTI O PRODUKTU

Height dimensions are without base/plinth.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE