


Varistar CP 19" Panel/Slide Mount, RAL 9005, 47 U, 2200H

Data Solutions

KATALOGOVÉ ČÍSLO

24630-014



Slide mount with adjustable increments. Assembly in 600 mm wide cabinets directly on the frame. At 800 mm width adapter bracket for reduced width is necessary, for partial-height mounting depth members are necessary.

VLASTNOSTI

19" panel/slide mount with U indicator

Depth-adjustable in 25 mm increments

In accordance with IEC 60297-1 (DIN 41 494, Part 1)

VLASTNOSTI PRODUKTU

Rack Height: 47U

Výška: 2200mm

Množství v balení: 4

Barva: Jet Black

Kód barvy: RAL 9005

Povrchová úprava: Strukturovaný Práškový

Materiál: Ocel

Produktová řada: Varistar CP

Product Type: Slide Mount

Net Weight: 19.338kg

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE