

Monitor, Keyboard, Touchpad, 1 U Drawer, Reduced Depth, English Keyboard

Data Solutions

KATALOGOVÉ ČÍSLO

60118-583



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



VLASTNOSTI

Pull-out 17" TFT color monitor chassis, 1 U (resolution Full HD; connects to VGA or DVI-D interface)

Keyboard with different keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 450 ... 640 mm

With DVI connection

VLASTNOSTI PRODUKTU

Rack Height: 1U

Barva: Jet Black

Kód barvy: RAL 9005

Hloubka: 400mm

Product Type: Cabinet/Rack Drawer

Typ: Monitor, Keyboard, Touchpad

Works With: 19" Cabinets

Keyboard Type: QWERTY UK

Net Weight: 13.3kg

DALŠÍ PODROBNOSTI O PRODUKTU

Further versions on request – With trackball or numeric pad.

Other Keyboard layouts see user manual.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE