


Intelligent iPDU, EN1812, 400 VAC, 3-PH, 32 A

Data Solutions

KATALOGOVÉ ČÍSLO

EN1812



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

VLASTNOSTI

Enlogic EN1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

VLASTNOSTI PRODUKTU

Produktová řada: Enlogic

Typ: Intelligent PDU

Product Type: Socket Strip

Typ zásuvky: (36) C13; (12) C19

Socket Quantity: 48

Barva: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 6

Input Cable Location: Top Feed

Input Voltage: 400V

Phase: 3 PH WYE

Max Power Input: 22.0 kVA

Output Voltage: 200 – 240VAC

Amperage (Derated Amperage): 32 A

Plug Type: IEC 60309 532P6 (IP44)

Rack Units: 0U

Removable Input Cable: No

Metering Type: Input

Množství v balení: 1

Interrupt Rating: 5kAIC

DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE