


# MI PDU, 1U, 30A(24A)NA/32A Int, 380-415V, 3P Wye, 9 CB, (9)4-in-1

## Data Solutions

### KATALOGOVÉ ČÍSLO

### EN1862



The Advantage Series Input Metered PDU family offers energy metering with advanced power and environmental monitoring options. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

### VLASTNOSTI PRODUKTU

Produktová řada: Enlogic

Product Type: Socket Strip

Typ zásuvky: (9) C13/C15/C19/C21

Barva: Black

Switched Outlets: No

Circuit Breaker: 20 A

Length: 43mm

Power Rating: 17.3 kVA North America; 22.1 kVA International

Circuit Breaker Quantity: 9

Input Voltage: 380 – 415V

Phase: 3 PH

Number of Poles: 1

Output Voltage: 208 – 230VAC

Nominální napětí: 415V

Plug Type: IEC 60309 530P6 (IP44)

Removable Input Cable: No

Amperage (Derated Amperage): 30 A (24 A) North America; 32 A International

Povrchová úprava: Strukturovaný Práškový

Rack Units: 1U

Materiál: Ocel

Metering Type: Input

Typ: Intelligent PDU

Výška: 43mm

Šířka: 444mm

Hloubka: 269mm

Hmotnost: 8kg

Množství v balení: 1

Input Cable Length: 1.8m

## DALŠÍ PODROBNOSTI O PRODUKTU

---

43 mm L x 444 mm W x 269 mm D, (269 mm D at CB)

## UPOZORNĚNÍ

---

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**