

Intelligent iPDU, EN6812, 400 VAC, 3-PH, 32 A

Data Solutions

KATALOGOVÉ ČÍSLO

EN6812

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

VLASTNOSTI

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

VLASTNOSTI PRODUKTU

Produktová řada: Enlogic

Typ: Intelligent PDU

Product Type: Socket Strip

Typ zásuvky: (36) C13; (12) C19

Socket Quantity: 48

Barva: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: Yes

Circuit Breaker Quantity: 6

Current Rating: 32A

Input Cable Location: Top Feed

Max Power Input: 22.0 kVA

Input Voltage: 400V

Phase: 3 PH WYE

Output Voltage: 200 – 240VAC

Plug Type: IEC 60309 532P6 (IP44)

Amperage (Derated Amperage): 32 A

Removable Input Cable: No

Rack Units: 0U

Metering Type: Outlet

Množství v balení: 1

Interrupt Rating: 5kAIC

DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE