

CPCI Backplane

The nVent SCHROFF CompactPCI Backplanes have best in class signal integrity and MTBF values due to SMD components, ceramics capacitors and press fit connectors.



CERTIFICATIONS



VLASTNOSTI

Digital GND can be connected to/isolated from chassis GND by means of screws

V(I/O) can be set to +3.3 V or +5 V

Outer layers act as GND surfaces

Utility plug for status signals (SMCQ)

Outstanding high frequency noise suppression and very high MTBF values due to ceramic capacitors

Intelligent platform management bus (IPMB) connector to PICMG 2.9

SPECIFIKACE

Table 1/2

Katalogové číslo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23006-794	Backplane	2	9U	CompactPCI, 64-bit	Left	4HP
23006-799	Backplane	4	7U	CompactPCI, 64-bit	Left	4HP
23006-798	Backplane	6	7U	CompactPCI, 64-bit	Left	4HP

Katalogové číslo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23006-797	Backplane	8	9U	CompactPCI, 64-bit	Left	4HP
23006-796	Backplane	6	9U	CompactPCI, 64-bit	Left	4HP
23006-795	Backplane	4	7U	CompactPCI, 64-bit	Left	4HP
23006-793	Backplane	2	7U	CompactPCI, 64-bit	Left	4HP
23006-792	Backplane	2	7U	CompactPCI, 64-bit	Left	4HP
23006-611	Backplane	8	9U	CompactPCI, 64-bit, PSB, H.110 Bus	Left	4HP
23006-601	Backplane	8	6U	CompactPCI, 64-bit, H.110 Bus	Right	4HP

Table 2/2

Katalogové číslo	Voltage I/O	Connector Type	Power Connector Type	Utility Connector Type	Šířka	Množství v balení
23006-794	5V	HM 2.0	(1) P47	SMCQ, 12-pin	39.64mm	1
23006-799	5V	HM 2.0	Mini-fit 24-pin	SMCQ, 12-pin		1
23006-798	5V	HM 2.0	Mini-fit 24-pin	SMCQ, 12-pin	121mm	1
23006-797	5V	HM 2.0	(2) P47	SMCQ, 12-pin	161.56mm	1
23006-796	5V	HM 2.0	(2) P47	SMCQ, 12-pin	121mm	1
23006-795	5V	HM 2.0	(2) P47	SMCQ, 12-pin		1
23006-793	5V	HM 2.0	Mini-fit 10-pin	SMCQ, 12-pin	39.64mm	1
23006-792	5V	HM 2.0	ATX (male) Connector		39.64mm	1
23006-611	5V	HM 2.0	(2) P47	SMCQ, 12-pin	161.56mm	1
23006-601	5V	HM 2.0	Power Bugs for M4 Cable Lugs	SMCQ, 12-pin	161.56mm	1

DALŠÍ PODROBNOSTI O PRODUKTU

Other configurations available on request.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE