

Front Panel, Front Shielded, Side Hinged

Front panel with textile EMC gasket, side hinged assembly.



CERTIFICATIONS



VLASTNOSTI

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right

SPECIFIKACE

Hloubka (D):	2.5mm
Rack Width:	84HP
Materiál:	Hliník
Povrchová úprava:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Typ:	Front Panel without Handle
EMC Shielding:	No (Retrofittable)


Table 1/2

Katalogové číslo	Rack Height	Množství v balení	Mounting	Gasket Type	Front Finish	Rear Finish
20848-611	3U	1	Hinged, Side	Textile EMC	Anodized	Conductive
20848-617	6U	1	Hinged, Side	Textile EMC	Anodized	Conductive

Table 2/2

Katalogové číslo	Treated Edges	Výška (H)	Šířka (W)
20848-611	No	128.4mm	426.4mm
20848-617	No	261.8mm	426.4mm

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE