

nVent CADDY EZ Riser, 4" Pipe

KATALOGNUMMER

EZR0400



The nVent CADDY EZ Riser is a multi-purpose clamp designed to secure and support vertical pipe runs. This unified solution can be installed in several approved orientations and serves as a standard, standoff, or close-quarters riser—effectively functioning as three clamps in one. Ready-to-use out of the box, the nVent CADDY EZ Riser features pre-drilled threaded rod holes for standoff installations and score marks for simple ear removal in spaces where full-sized riser clamps do not fit.

Contractors can enjoy simplified material handling with a multi-functional clamp that allows for various orientations and retains listing even when ears are removed.

CERTIFICERINGER



FUNKTIONER

Only one tool needed to tighten due to serrated wash-heads

Installs up to 60% faster than standard riser clamps

Integrated second set of bolt holes allow the assembly to adapt from a riser clamp into a stand-off support easily

No need to stock and use separate part families for standard and close-quarter clamps to offer a full range of listed parts

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

PRODUKTEGENSKABER

Artikelnummer: 179234

Materiale: Stål

Finish: Electrogalvanized

Pipe Size: 4"

Outer Diameter (OD): 114.3 mm

Hole Size (HS): 13.2 mm

A: 330.2 mm

B: 254 mm

C: 31.8 mm

Static Load: 3600N

YDERLIGERE PRODUKTOPLYSNINGER

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Use of a socket or driver is recommended for installation.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

