

Macrofix Non-Insulated M8/M10, 54–62 mm OD, 2" Pipe, 50 DN

KATALOGNUMMER

MFN062EG



CERTIFICERINGER



FUNKTIONER

Plastic washer prevents screws from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

PRODUKTEGENSKABER

Artikelnummer: 586108

Materiale: Stål

Finish: Electrogalvanized

Outer Diameter (OD): 54 - 62 mm

Pipe Size: 2" Min

NB/DN: 50

Rod Size (RS): M8;M10

Width (W): 20 mm


Thickness (T): 1.25 mm

Screw Diameter (Sc): 6

Screw Length (L): 22mm

Static Load: 1500N

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

