

nVent CADDY Macrofix Plus Kombi with Combination Nut, M8,M10,1/2"Rod, 78-88mm OD

KATALOGNUMMER

MPK088



FUNKTIONER

Includes easy closing mechanism

Age-resistant lining

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

PRODUKTEGENSKABER

Artikelnummer: 586761

Rod Size (RS): M8;M10;1/2"

Temperature: -50 to 110 °C

Farve: Black

Materiale: Stål;EPDM-SBR Rubber

Finish: Electrogalvanized

Outer Diameter (OD): 78 - 88 mm

Width (W): 23 mm

Thickness (T): 1.5 mm

Screw Diameter (Sc): 6 mm

Screw Length (L): 40mm


Static Load: 2000N

Unit Weight: 0.2 kg

YDERLIGERE PRODUKTOPLYSNINGER

Lining is EPDM rubber.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

