


Oval Sleeve



The nVent CADDY Oval Sleeve is a fast and effective way to secure cable to rooftop equipment. By utilizing the nVent CADDY Manual Swaging Tool, contractors working on rooftops or in the shop can now benefit from a full-service solution designed for durability and longevity throughout high and low temperatures. Made to secure various rooftop equipment such as metal ducts, HVAC units, piping and walkways.

CERTIFICERINGER



FUNKTIONER

Designed to be used exclusively with size 3/16 stainless steel nVent CADDY Pyramid Rooftop Anchor Cable Bracing and nVent CADDY Manual Swaging Tool

Versatile solution designed for on-site and in-shop use

Stainless steel is corrosion and harsh weather-resistant

SPECIFIKATIONER

Materiale: Copper

Finish: Electrogalvanized

Table 1/1

| Katalognummer | Artikelnummer | Brace Size |
|---------------|---------------|------------|
| CSB12SLVB | 402194 | #12 |
| CSB18SLVB | 402195 | #18 |
| CSB36SLVB | 402196 | #36 |

YDERLIGERE PRODUKTOPLYSNINGER

Two side-by-side swages required on #12 and #18 cable. Three side-by-side swages required on #36 and #48 cable.

Check swage with gauge (not included).

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

