

Threaded Bridle Ring



FUNKTIONER

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

SPECIFIKATIONER

Finish: Electrogalvanized

Materiale: Stål

Table 1/1

Katalognummer	Artikelnummer	Diameter	Screw Diameter	Screw Type	Screw Length	Ultimate Static Load
PTB6	172921	12 mm	6	Metal	32mm	220N
PTB8	172922	16 mm	8	Metal	32mm	220N
GR50	172920	50 mm	6	Metal	18mm	220N

YDERLIGERE PRODUKTOPLYSNINGER

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

