

Cadweld Multi Multiple Connection Type Mold Kit

Data Solutions

KATALOGNUMMER

KITCDMV01



FUNKTIONER

Versatile mold produces a variety of connections

Patented, self-sealing system prevents weld metal leakage

Compact compression structure enables easy alignment of conductors

Language-free instruction guide

Easy-to-use system completes welds in seconds

PRODUKTEGENSKABER

Artikelnummer: 167782

Complies With: EN IEC® 62561-1 permanent connection

Types of ERICO CADWELD MULTI Multiple Connectors							
Mold Style	Number of Battings Required	Maximum Conductor Size	Maximum Bus/Lug Size	Maximum Rebar Size, Metric	Maximum Rebar Size, US	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual
Solid or Stranded Copper Cable to Solid or Stranded Copper Cable							
SS	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
SC	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
XA	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GG	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GJ	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GF	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GW	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
XB	3	50 mm ² Str; 1/0 Str	-	-	-	-	-
PP	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PK	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
GE	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
PG	2	50 mm ² Str; 1/0 Str	-	-	-	-	-
TD	2	25 mm ² Str; #4 Str	-	-	-	-	-
TE	2	25 mm ² Str; #4 Str	-	-	-	-	-
TF	2	25 mm ² Str; #4 Str	-	-	-	-	-
Solid or Stranded Copper Cable to Rebar							
RG	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RH	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RK	2	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
RD	3	50 mm ² Str; 1/0 Str	-	10 mm	#3	-	-
Copper or Steel Tape to Rebar							

RF	2	-	30 x 3.5 mm	10 mm	#3	-	-
Copper Tape to Copper Tape							
BB	2	-	30 x 3.5 mm	-	-	-	-
CG	3	-	30 x 3.5 mm	-	-	-	-
BG	3	-	30 x 3 mm	-	-	-	-
EB	3	-	30 x 3 mm	-	-	-	-
Solid or Stranded Copper Cable to Copper or Steel Bus/Lug							
HA	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HC	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HS	3	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
HT	3	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
GL	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LA	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LJ	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
LE	2	50 mm ² Str; 1/0 Str	30 x 3.5 mm	-	-	-	-
Galvanized Steel Tape to Galvanized Steel Tape							
BB	2	-	30 x 3 mm	-	-	-	-
CG	3	-	30 x 3 mm	-	-	-	-
Solid or Stranded Copper Cable to Ground Rods							
TG	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GT	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GR	2	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GT	3	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
GR	3	10mm ² Str; #6 Str	-	-	-	1/2" - 3/4"	12.8 - 17.3 mm
Copper Tape to Ground Rod							
CN	2	-	30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	2	-	30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CN	3	-	30 x 2.5 mm - 30 x 3 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	3	-	30 x 2.5 mm - 30 x 3 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
Galvanized Steel Tape to Ground Rod							

CN	3	-	30 x 0.5 mm - 30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm
CP	3	-	30 x 0.5 mm - 30 x 3.5 mm	-	-	1/2" - 3/4"	12.8 - 17.3 mm

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE