

Neutral Bar for TD Distribution Blocks, 160 A IEC

Data Solutions

KATALOGNUMMER

NB-160A



CERTIFICERINGER



FUNKTIONER

Attaches to four pole distribution blocks for increased wire capacity

Direct electrical connection

Strong mechanical assembly

Transparent protection cover

Halogen free

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

PRODUKTEGENSKABER

Artikelnummer: 563201

Max Current Rating, IEC: 160A

Short Term Withstand Current (I_{cw}) 1s: 6.2kA

Peak Short Circuit Current (I_{pk}): 35kA

Line Side Number of Connections: 4

Line Side Compact Stranded Wire Size: 10 - 35 mm²

Line Side Stranded Wire Size - Ferrule: 10 – 25mm²

Load Side Number of Connections: 10

Load Side Compact Stranded Wire Size: 2,5 - 16 mm²

Load Side Stranded Wire Size - Ferrule: 1,5 – 16 mm²

Dybde (D): 41.4mm

Height (H): 34.3mm

Width (W): 170mm


Unit Weight: 0.2kg

For Use With: TD-160A (563200); TD-160AL (563990)

Flammability Rating: UL® 94V-0

Complies With: IEC® 60947-7-1

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE