

Cable to Web of Rail Complete Welder, Power, 85-141 lb T-Rail, 2/0 Ropelay, Right Hand

Data Solutions

KATALOGNUMMER

PBWT202JRH



FUNKTIONER

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

PRODUKTEGENSKABER

Materiale: Graphite; Stål; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 2/0 Ropelay

Conductor Outer Diameter, Nominal: 12.19mm

Welder Style: T20

Orientation: Right Hand

Mold Only: No

Replacement Mold: PBW2JRH

Welding Material: PB90, Sold Separately

Handle Clamp: C105C, Sold Separately

Conductor Sleeve: S06F, Sold Separately

Hammer Die: WD84, Sold Separately

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE