

Compression Straight Lug, Standard, 2/0 Stranded, 70 mm² Stranded, 13 mm Hole

Data Solutions

KATALOGNUMMER

RKS7012T



FUNKTIONER

Tin plated for corrosion prevention

Annealed copper eases the crimping operation

Optimized sizes to the most efficient electrical conductivity

Best mechanical behavior (vibration/pull-out); DIN EN 61373 Class 1B "Railway Applications"

Markings on barrel for crimping

Consistent material thickness, precise diameter and accurate cable fit; DIN46235

PRODUKTEGENSKABER

Artikelnummer: 716656

Materiale: Copper

Finish: Tinned

Lug/Connector Type: Standard

Conductor Size: 2/0 Stranded; 70 mm² Stranded


Hole Size (HS): 13mm

Length (L): 59mm

Width (W): 23mm

Tool/Die Type: M2M or M2H/RKM2; M3H or M3B/RKM3; MLB/RKML

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE