

Outdoor Modular 29 U 1530H 900W 1100D

Data Solutions

KATALOGNUMMER

10149-677



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

FUNKTIONER

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from front, all sides possible upon request

100 mm high plinth, 200 and 300 mm possible

Top cover with louvers, can be upgraded with fans or A/C unit

RAL 7035 powder coating, other colors available upon request

PRODUKTEGENSKABER

Product Type: Outdoor Cabinet

Produktfamilie: Modular

Rack Height: 29U

Højde: 1530mm

Bredde: 900mm

Dybde: 1100mm

Wall Type: Double Walled

Door Type: Plain; Double Door

Cooling: Passive

EMC Shielding: Optional

Pakke mængde: 1

Battery Compartment: Optional

Burglar Resistance: Optional

Finish: Struktur Pulvermaling

Frame Material: Aluminium

Materiale: Aluminium; Stål

Plinth Height: 100mm

Mounting Setup: Optional

YDERLIGERE PRODUKTOPLYSNINGER

Height dimensions are without base/plinth.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE