

19" Drawer, 2 U, Front Panel Anodized

Data Solutions

KATALOGNUMMER

20110-062



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

CERTIFICERINGER



FUNKTIONER

Static load-carrying capacity 15 kg

Optional writing surface

PRODUKTEGENSKABER

Rack Height: 2U

Finish: Struktur Pulvermaling

Pakke mængde: 1

Front Finish: Anodized

Type: Drawer

Materiale: Stål

Product Type: Cabinet/Rack Drawer

Static Load: 15kg

Works With: 19" Cabinets

Net Weight: 8.1kg

YDERLIGERE PRODUKTOPLYSNINGER

Please order 19" assembly kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE