

Varistar CP Glazed Door, With 1-Point Locking, Key Plate Only, RAL 7021, 24 U, 1200H 600W

Data Solutions

KATALOGNUMMER

21630-481



Varistar CP Glass Door Single Point Locking for IP 20 applications.

FUNKTIONER

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

PRODUKTEGENSKABER

Rack Height: 24U

Højde: 1200mm

Bredde: 600mm

Locking Type: Single Point Locking

Pakke mængde: 1

Farve: Black Grey

Farvekode: RAL 7021

Complies With: IEC 61587-1

Finish: Struktur Pulvermaling

Materiale: Stål; Glass

Produktfamilie: Varistar CP

Product Type: Cabinet Door

Beskyttelsesgrad: IP20

Type: Glass Door

Works With: Varistar CP

Net Weight: 18.506kg

YDERLIGERE PRODUKTOPLYSNINGER

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE