

Telescopic Slides C-Profile for Cabinet for Fitting LABRACK, 250 mm

Data Solutions

KATALOGNUMMER

24562-446



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

CERTIFICERINGER



FUNKTIONER

For mounting 84 HP wide subracks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the subrack (it is inserted into the guiding profile like a telescopic slide)

PRODUKTEGENSKABER

Produktfamilie: Labrack

Dybde: 250mm

Pakke mængde: 2

Finish: Anodized

Materiale: Aluminium

Product Type: Telescopic Slide

Type: C Profile

Gross Weight: 0.304kg

YDERLIGERE PRODUKTOPLYSNINGER

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE