

19" Front Panel With Holes for Handles, 5 U, 3 mm, Al, Anodized, Untreated Edges

Data Solutions

KATALOGNUMMER

30219-165



Define the device fronts and side inss with Schroff 19" front panels. Schroff 19" front panels have additional holes for mounting of handles and are available in 1 U to 6 U demensions.

CERTIFICERINGER



FUNKTIONER

19" front panels have additional holes for mounting of handles

PRODUKTEGENSKABER

Rack Height: 5U

Dybde (D): 3mm

Accessory Type: Front panel

Håndtagstype: Front Handle

Finish: Anodized

Mounting: Screw-on Front

Pakke mængde: 1

Front Finish: Anodized

Rear Finish: Anodized

Treated Edges: No

EMC Shielding: No

Højde (H): 221.4mm

Materiale: Aluminium

Product Type: Front Panel

Rack Width: 95HP

Type: 19" Front Panel

Bredde (W): 483mm

Net Weight: 0.83kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE