

Monitor, Keyboard, Touchpad, 1 U Drawer, German Keyboard

Data Solutions

KATALOGNUMMER

60118-581



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICERINGER



FUNKTIONER

Pull-out 17" TFT color monitor chassis, 1 U (resolution 1280 x 1024; connects to VGA interface)

Keyboard with different language keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 470 ... 740 mm

PRODUKTEGENSKABER

Rack Height: 1U

Pakke mængde: 1

Farve: Jet Black

Farvekode: RAL 9005

Dybde: 470mm

Product Type: Cabinet/Rack Drawer

Type: Monitor, Keyboard, Touchpad

Works With: 19" Cabinets

Keyboard Type: QWERTZ

Net Weight: 15.4kg

YDERLIGERE PRODUKTOPLYSNINGER

Further versions on request. With trackball or numeric pad.

Other Keyboard layouts see user manual.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE