

Basic PDU, EB0305, 230 VAC, 1-PH, 63 A

Data Solutions

KATALOGNUMMER

EB0305

Modular, compact PDU. Ultra-Low Profile Design

FUNKTIONER

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUKTEGENSKABER

Produktfamilie: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Stiktype: (6) C19

Socket Quantity: 6

Farve: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 6

Input Cable Location: Front Feed

Input Voltage: 200 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 14.4 kVA

Output Voltage: 200 – 240VAC

Amperage (Derated Amperage): 63 A

Plug Type: IEC 60309 363P6 (IP44)

Rack Units: 1U

Removable Input Cable: No

Metering Type: None

Pakke mængde: 1

Input Cable Length: 3m

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE