

Basic PDU, EB0322, 230 VAC, 1-PH, 16 A

Data Solutions

KATALOGNUMMER

EB0322



Modular, compact PDU. Ultra-Low Profile Design

FUNKTIONER

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUKTEGENSKABER

Produktfamilie: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Stiktype: (20) C13; (2) C19

Socket Quantity: 22

Farve: Black

Circuit Breaker: No Circuit Breaker

Switched Outlets: No

Circuit Breaker Quantity: 0

Power Rating: 3.7 kVA

Input Cable Location: Top Feed

Input Voltage: 100 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 3.68 kVA

Nominal spænding: 230V

On/Off Switch Included: No

Output Voltage: 230VAC

Amperage (Derated Amperage): 16 A

Plug Type: IEC 60309 316P6 (IP44)

Rack Units: 0U

Removable Input Cable: Yes

Metering Type: None

Materiale: Stål

Finish: Struktur Pulvermaling

Højde: 817mm

Bredde: 52mm

Dybde: 53mm

Vægt: 3.61kg

Pakke mængde: 1

Input Cable Length: 3m

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE