

PDU, 0U, 32A, 230V, 1P, 2 CB, (16)C13, (4)4-in-1

Data Solutions

KATALOGNUMMER

EB0360



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

FUNKTIONER

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

PRODUKTEGENSKABER

Produktfamilie: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Stiktype: (16) C13/C15

Socket Quantity: 20

Farve: Black

Switched Outlets: No

Cable Length: 3000mm

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Power Rating: 7.4 kVA

Circuit Breaker Quantity: 2

Interrupt Rating: 5kAIC

Nominal Power Output: 230VAC

Nominal spænding: 230V

Number of Output Voltages: 20

Antal faser: 1

On/Off Switch Included: No

Amperage (Derated Amperage): 32 A

Output Voltage: 230VAC

Rack Units: 0U

Plug Type: IEC 60309 332P6 (IP44)

Metering Type: None

Removable Input Cable: No

Materiale: Stål

Finish: Struktur Pulvermaling

Højde: 817mm

Bredde: 52mm

Dybde: 53mm

Vægt: 3.6kg

Pakke mængde: 1

Input Cable Length: 3m

YDERLIGERE PRODUKTOPLYSNINGER

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE