

Basic PDU, EB0450, 400 VAC, 3-PH, 16 A

Data Solutions

KATALOGNUMMER

EB0450



Modular, compact PDU. Ultra-Low Profile Design

FUNKTIONER

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUKTEGENSKABER

Produktfamilie: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Stiktype: (21) C13/C19

Socket Quantity: 42

Farve: Black

Circuit Breaker: No Circuit Breaker

Switched Outlets: No

Circuit Breaker Quantity: 0

Power Rating: 11.5 kVA North America; 11.0 kVA International

Input Cable Length: 1.8m

Input Cable Location: Top Feed

Input Voltage: 380 – 415V

Phase: 3 PH

Nominal spænding: 415V

Max Power Input: 11.5 / 11.0 kVA

On/Off Switch Included: No

Amperage (Derated Amperage): 20 A (16 A) North America; 16 A International

Output Voltage: 208 – 230VAC

Rack Units: 0U

Plug Type: IEC 60309 520P6/516P6

Metering Type: None

Removable Input Cable: No

Materiale: Stål

Finish: Struktur Pulvermaling

Højde: 1490mm

Bredde: 56mm

Dybde: 55mm

Vægt: 9.5kg

Pakke mængde: 1

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE