

MI PDU, 1U, 16A, 230V, 1P, (9)C13/C15/C19/C21

Data Solutions

KATALOGNUMMER

EN1361

The Advantage Series Input Metered PDU family offers energy metering with advanced power and environmental monitoring options. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

FUNKTIONER

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

UL 2900-1 certified for safety software cybersecurity for network-connectable products.

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs

Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

PRODUKTEGENSKABER

Produktfamilie: Enlogic

Type: Intelligent PDU

Product Type: Socket Strip

Stiktype: (9) C13/C15/C19/C21

Socket Quantity: 9

Farve: Black

Switched Outlets: No

Cable Length: 3000mm

Power Rating: 3.7 kVA

Circuit Breaker: No Circuit Breaker

Circuit Breaker Quantity: 0

Phase: 1 PH

Nominal Power Output: 230VAC

Nominal spænding: 230V

Number of Output Voltages: 12

On/Off Switch Included: No

Output Voltage: 230VAC

Amperage (Derated Amperage): 16 A

Plug Type: IEC 60309 316P6 (IP44)

Rack Units: 1U

Removable Input Cable: Yes

Metering Type: Input

Materiale: Stål

Finish: Struktur Pulvermaling

Højde: 43mm

Bredde: 444mm

Dybde: 269mm

Vægt: 4.4kg

Pakke mængde: 1

Input Cable Length: 3m

YDERLIGERE PRODUKTOPLYSNINGER

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE