

Intelligent iPDU, EN1880, 400 VAC, 3-PH, 32 A

Data Solutions

KATALOGNUMMER

EN1880

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FUNKTIONER

Enlogic EN1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

PRODUKTEGENSKABER

Produktfamilie: Enlogic

Type: Intelligent PDU

Product Type: Socket Strip

Stiktype: (21) Locking C13/C15; (21) Locking C13/C15/C19/C21

Socket Quantity: 42

Farve: Black

Circuit Breaker: 20 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 6

Power Rating: 17.3 kVA North America; 22.1 kVA International

Input Cable Length: 1.8m

Input Cable Location: Top Feed

Input Voltage: 380 – 415V

Phase: 3 PH

Max Power Input: 17.3 / 22.1 kVA

Nominal spænding: 415V

On/Off Switch Included: No

Output Voltage: 208 – 230VAC

Amperage (Derated Amperage): 30 A (24 A) North America; 32 A International

Plug Type: IEC 60309 530P6/532P6

Rack Units: 0U

Removable Input Cable: No

Metering Type: Input

Materiale: Stål

Finish: Struktur Pulvermaling

Højde: 1826mm

Bredde: 56mm

Dybde: 55mm

Vægt: 11.02kg

Pakke mængde: 1

Gross Weight: 10kg

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE