


# MSP0 PDU, 2U, 60A(48A), 208V, 3P Delta, 6 CB, (9)C13, (9)4-in-1

## Data Solutions

### KATALOGNUMMER

**EN6963**



The Advantage Series Outlet Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at the input phase, circuit breaker, and individual outlet levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

### PRODUKTEGENSKABER

Produktfamilie: Enlogic

Product Type: Socket Strip

Stiktype: (9) C13/C15; (9) C13/C15/C19/C21

Circuit Breaker: 20 A

Farve: Black

Circuit Breaker Quantity: 6

Switched Outlets: Yes

Length: 87mm

Power Rating: 17.3 kVA

Interrupt Rating: 10kAIC

Number of Poles: 2

Input Voltage: 208V

Phase: 3 PH Delta

Output Voltage: 208VAC

Plug Type: IEC 60309 460P9 (IP44)

Nominal spænding: 208V

Removable Input Cable: No

Amperage (Derated Amperage): 60 A (48 A)

Rack Units: 2U

Type: Intelligent PDU

Finish: Struktur Pulvermaling

Metering Type: Outlet

Materiale: Stål

Højde: 87mm

Vægt: 9kg

Bredde: 444mm

Dybde: 269mm

Pakke mængde: 1

Input Cable Length: 1.8m

## YDERLIGERE PRODUKTOPLYSNINGER

---

87 mm L x 444 mm W x 269 mm D, (269 mm D at CB)

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**