

Motion detector

Data Solutions



Motion detector: Prepared for mounting on door box, detection method: movement, detection fields of radar are adjustable, wide field 4 m (W) x 2 m (D), narrow field 2 m (W) x 2.5 m (D), supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate.

CERTIFICERINGER



FUNKTIONER

Supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate

Wide field 4 m (W) x 2 m (D)

Arrow field 2 m (W) x 2.5 m (D)

Detection method: movement

Prepared for mounting on door box

Detection fields of radar are adjustable

SPECIFIKATIONER

Table 1/1

Katalognummer	Type	Works With	Pakke mængde
60130-067	Motion Detector	Aisle Containment	1

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE