

CABS Module Kit



CERTIFICERINGER



FUNKTIONER

Modules provide flexibility to select distance between phases and supports

Installs quickly and easily

Halogen free insulators

RoHS compliant

SPECIFIKATIONER

Typical Application Current Rating:	400 - 4500 A
Max Working Voltage, IEC (Ui):	1000;1500
Working Temperature:	-40 to 130 °C
Finish:	Electrogalvanized
Materiale:	Stål;Glass Fibre Reinforced Polyamide
Complies With:	IEC® 60439.1;IEC® 61439.1;IEC® 60695-2-11 (Glow Wire Test 960 °C)
Flammability Rating:	UL® 94V-0

Table 1/2

Katalognummer	Artikelnummer	Busbars per Phase	Busbar Width	Busbar Thickness	Dybde (D)	Width (W)
---------------	---------------	-------------------	--------------	------------------	-----------	-----------

CABS4-5T-MOD	549370	1 - 4	30 - 125 mm	5 mm	39mm	75 mm
CABS2-10T-MOD	549380	1 - 2	30 - 120 mm	10 mm	39mm	75 mm
CABS3-10T-MOD	549390	1 - 3	30 - 120 mm	10 mm	39mm	100 mm

Table 2/2

Katalognummer	Artikelnummer	Unit Weight
CABS4-5T-MOD	549370	0.39 kg
CABS2-10T-MOD	549380	0.37 kg
CABS3-10T-MOD	549390	0.45 kg

YDERLIGERE PRODUKTOPLYSNINGER

CABS modules must be installed on CABS-APP Aluminium Profile.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE