

ATCA Front Panel Kit With Spring Loading



AdvancedTCA front panel for spring-loaded IEA handle (plunger or lever style) with die-cast end piece in Al-Profile or stainless material.

CERTIFICERINGER



FUNKTIONER

Front panel (reinforced with diecast endpiece)

ATCA IEA handle with spring loading

EMC textile gasket and fixing material

SPECIFIKATIONER

Rack Width:	6HP
Rack Height:	8U
Accessory Type:	Front panel
Product Type:	Front Panel


Table 1/2

Katalognummer	Materiale	Finish	Pakke mængde	Front Finish	Rear Finish	Dybde (D)
20818-160	Stainless Steel		1	Raw	Raw	1mm
20818-169	Aluminium	Passivated	1	Raw	Raw	1mm
20818-161	Stainless Steel		1	Raw	Raw	1mm
20818-170	Aluminium	Passivated	1	Raw	Raw	1mm

Table 2/2

Katalognummer	Højde (H)	Bredde (W)
20818-160	323.15mm	28.95mm
20818-169	323.15mm	28.95mm
20818-161	323.15mm	28.95mm
20818-170	323.15mm	28.95mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE