

CompacPRO Rear Panel With Vented Slots

The rear panel with vented slots can be used for the CompacPRO case. The rear panel is bolted on the rear frame.



CERTIFICERINGER



FUNKTIONER

Al material 3.0 mm

SPECIFIKATIONER

Materiale:	Aluminium
Finish:	Anodized
Works With:	Cases
Produktfamilie:	CompacPRO
Type:	Rear Panel
Product Type:	Side Panel

Table 1/1

Katalognummer	Rack Height	Rack Width	Pakke mængde
30823-027	3U	63HP	1
30823-033	4U	42HP	1
30823-036	4U	63HP	1
30823-021	3U	28HP	1
30823-024	3U	42HP	1

Katalognummer	Rack Height	Rack Width	Pakke mængde
30823-518	4U	84HP	1
30823-512	2U	84HP	1
30823-045	6U	63HP	1
30823-015	2U	42HP	1
30823-521	6U	84HP	1
30823-515	3U	84HP	1

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE