

# CPCI PlusIO Backplane



CompactPCI PlusIO combines the legacy CompactPCI and the new, high speed CompactPCI Serial Technology on one backplane. The CompactPCI PlusIO system slot addresses both, the parallel PCI bus as well as the CompactPCI Serial slots with PCIe, USB, Ethernet and S-ATA.

## CERTIFICERINGER



## FUNKTIONER

In accordance with: PICMG 2.0 R3.0 CompactPCI Core Specification, PICMG 2.1 R2.0 Hot-Swap Specification, PICMG 2.9 R1.0 System Management Bus Specification, PICMG 2.10 R1.0 Keying Specification, PICMG 2.30 R1.0 CompactPCI PlusIO specification, PICMG CompactPCI Serial (CPCI-S.0 R1.0) specification

System slot in accordance with PICMG 2.30, 32-bit CPCI bus on P1, PCIe, S-ATA, USB & Ethernet on P2

CompactPCI peripheral slots, 32 bit with rear I/O on P2

Rear I/O on the CompactPCI Serial slots available on request

CompactPCI Serial peripheral slots with PCIe x1, S-ATA and USB

Full-mesh Ethernet on system slot and 2 CompactPCI Serial slots, supports 1000Base-T and 10GBase-T

V(I/O) can be set to 3.3 V or 5 V (preset to 5 V)

## SPECIFIKATIONER

Table 1/2

Katalognummer	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-602	Backplane	5	3U	CompactPCI PlusIO, CompactPCI Serial	Middle	4HP

Katalognummer	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-601	Backplane	8	3U	CompactPCI PlusIO, CompactPCI Serial	Middle	4HP

Table 2/2

Katalognummer	Voltage I/O	Connector Type	Power Connector Type	Utility Connector Type	Bredde	Pakke mængde
23007-602	5V	HM 2.0, AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin	102.2mm	1
23007-601	5V	HM 2.0, AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin	161.3mm	1

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**