


MTCA.0 System for 10 Single Full-Size AMC Modules, 3 U, 84 HP

KATALOGNUMMER

11850-011



The double AMC card cage on the right hand side can hold either 4 Double Full-size AMCs or, with the optional splitting kit, 8 Single Full-size AMCs.

CERTIFICERINGER



FUNKTIONER

In accordance with PICMG MTCA.0 R1.0 specification

3 U, 19" subrack system for 10 Single Full-Size AdvancedMC modules, 2 Single Full-Size MCHs and 2 power modules with width up to 12 HP

Instead of 8 Single Full-Size AdvancedMC modules, the right-hand board cage can be used for 4 Double Full-Size modules

Backplane with dual star topology, direct connections for S-ATA/SAS

Clock topology to PICMG AMC.0 R2.0

Two hot-swap fan modules in push/pull configuration, each with cooling unit manager (CU EMMC), airflow from right to left

Air filter is front accessible, with presence signal

PRODUKTEGENSKABER

Product Type: System

Number of Slots: 8

Type: 19" Rack Mount

Backplane Type: MTCA.0 Dual Star Topology

Data Transfer: 40 GbE; PCIe Gen3

Power per Slot: 50W

Airflow Direction: Right to Left

Rack Height: 3U

Power Supply Type: (2) Single Full-size PM

Power Supply Included: No

Rear I/O: No

Complies With: PICMG MTCA.0 R2.0

Dybde: 216mm

Højde: 133.35mm

Net Weight: 7.9kg

Pakke mængde: 1

YDERLIGERE PRODUKTOPLYSNINGER

Modified systems available on request.

Completely assembled, wired and tested.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE