


PXI-Express System, 4 U, 8 slots, Gen 3

KATALOGNUMMER

14579-030



Desktop PXI Express Chassis for one PXI Express System Controller with up to 16 HP and 7 PXI or PXI Express Boards with 4 HP Width.

CERTIFICERINGER



FUNKTIONER

PXI Express Desktop Chassis, 4 U, 44 HP

1 PCIe System Slot an 7 Hybrid Slots

Ultra-high performance Gen 3 PCIe switching with a default four-link (4x4) System Slot

Powerful cooling concept with low fan noise, 50 W per slot @ 15K temperature increase

Air flow from bottom to rear with temperature controlled fans; Integrated Chassis Monitoring Modul (CMM)

Wide range AC input with mains switch on the rear side, power push button on the front (top)

Rear panel external 10 MHz clock inputs/outputs

PRODUKTEGENSKABER

Product Type: System

Number of Slots: 8

Type: Desktop

Backplane Type: PXI Express, 4 Link Configuration

Data Transfer: PCIe Gen3

Power per Slot: 50W

Indgangsspænding AC: 100 – 240V

Airflow Direction: Bottom to Rear

Rack Height: 4U

Power Supply Type: Open Frame

Power Supply Included: Yes

Rear I/O: No

Complies With: PXISA PXI-5 R1.1

PXI Express Timing Slot Quantity: 0

Dybde: 315mm

Net Weight: 8.1kg

Pakke mængde: 1

YDERLIGERE PRODUKTOPLYSNINGER

System in accordance with IEC 60297--3--101, --102, --103; IEEE 1101.1, 1101.10/11); Backplane, conforms to PICMG rev. 3.0 and PXI-5.

Modified systems available on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE