


Front Panel Kit, Unshielded, Bottom Hinged, 3 U, 84 HP, 2.5 mm, Al, Anodized

KATALOGNUMMER

20838-273



Unshielded front panel bottom hinged.

CERTIFICERINGER



FUNKTIONER

Front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

PRODUKTEGENSKABER

Rack Height: 3U

Accessory Type: Front panel

Rack Width: 84HP

Pakke mængde: 1

Mounting: Hinged, Bottom

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: No

Dybde (D): 2.5mm

Finish: Anodized

Materiale: Aluminium

Type: Front Panel without Handle

Gross Weight: 0.478kg

Front panel can be removed in opened position ($> 135^\circ$).

Technical drawing of a rectangular plate. The drawing shows a rectangle with various dimensions and tolerances. The overall width is labeled 'A' and the overall height is labeled 'H'. The top edge has a dimension of 7.45 with a tolerance of ± 0.1 . The bottom edge has dimensions of 15.6, 16, and 8.2. The right edge has a dimension of 3 with a tolerance of ± 0.1 . The left edge has a dimension of 3 with a tolerance of ± 0.1 . The top right corner has a dimension of 3 with a tolerance of ± 0.1 . The bottom right corner has a dimension of 3 with a tolerance of ± 0.1 . The drawing also shows a hole with a diameter of $\varnothing 5.9 \times 3.3$ and a hole with a diameter of $\varnothing 2.5$.

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Straubenhardt, Germany
 +49.7082.794.0
 Betschdorf, France
 +33.3.88.90.64.90
 Warsaw, Poland
 +48.22.209.98.35
 Assago, Italy
 +39.02.932.7141
 Chat with us:
nvent.com/schroff

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE