

Panhead Screw, Torx, Steel Zinc Plated, Precoated Thread, M2.5 x 6 mm

KATALOGNUMMER

24560-159



Pan head Torx screws with different metric threads and lengths. With optional features like GND earthing function or "precoated thread".

Panhead Screw, Torx, St, zinc plated, M2.5 x 6 (Partially coated thread to prevent the screw from loosening on its own due to vibrations).

CERTIFICERINGER



FUNKTIONER

Pan Head Screw with torx, self-locking

PRODUKTEGENSKABER

Length: 6mm

Finish: Forzinket Stål

Pakke mængde: 100

Thread Size: M2.5

Materiale: Stål

Product Type: Screw

Type: Panhead Screw

Works With: Backplanes; Test Adapters

Net Weight: 0.03kg

YDERLIGERE PRODUKTOPLYSNINGER

Torque max. 0.2 Nm.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE