

Series 311 Hard Anodize Inserter/Extractor

KATALOGNUMMER

HA311-TC



The rugged Series HA311 was designed in accordance with VITA 48.4 and 48.2 to provide up to 10:1 mechanical advantage for insertion and extraction of printed circuit boards with high density connector contacts. The integrated spring provides positive pressure on connectors during Card Lok actuation and consistent self-compensation for board tolerances. The Series 311-TC is ideal for 2nd level maintenance; can be operated with a gloved hand and no specialized tools are required.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

FUNKTIONER

Integrated latching mechanism

Custom silkscreen available

Provides self-compensation for board tolerances

Compliant with 2nd level maintenance; can be operated with a gloved hand, no specialized tools are required

Designed in accordance with VITA 48.4 and 48.2

Maintains positive pressure on connectors during Card Lok actuation

PRODUKTEGENSKABER

Product Type: PCB Inserter/Extractor

With Pin: No

Materiale: Aluminum Alloy 6061-T6

Finish: Hard Black Anodized

Design Feature: Tolerance Compensating

YDERLIGERE PRODUKTOPLYSNINGER

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE