

# Interscale Desktop Case, Non-Perforated

Flexible desktop case with integrated EMC protection. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.



## CERTIFICERINGER

---



## FUNKTIONER

---

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 30

Color RAL 7016

Modified or customized cases upon request

## SPECIFIKATIONER

---

<b>Materiale:</b>	Aluminium; Stål
<b>Type:</b>	Desktop
<b>Produktfamilie:</b>	Interscale
<b>Beskyttelsesgrad:</b>	IP30
<b>Farvekode:</b>	RAL 7016
<b>Product Type:</b>	Small Form Factor Case

Table 1/2

Katalognummer	Højde	Pakke mængde	Bredde	Dybde	Cooling	Farve
14820-133	43.7mm	1	132.6mm	132.6mm	Non-Perforated	Anthracite Grey
14820-297	88.1mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey
14820-255	88.1mm	1	221mm	221.45mm	Non-Perforated	Anthracite Grey
14820-295	88.1mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-154	43.7mm	1	221mm	177mm	Non-Perforated	Anthracite Grey
14820-375	132.6mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-254	88.1mm	1	221mm	177mm	Non-Perforated	Anthracite Grey
14820-155	43.7mm	1	221mm	221.45mm	Non-Perforated	Anthracite Grey
14820-395	132.6mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-134	43.7mm	1	133mm	177mm	Non-Perforated	Anthracite Grey
14820-195	43.7mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-175	43.7mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-275	88.1mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-397	132.6mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey
14820-197	43.7mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey

Table 2/2

Katalognummer	Finish
14820-133	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-297	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-255	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-295	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-154	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-375	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-254	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-155	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-395	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-134	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-195	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-175	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-275	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-397	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-197	Aluminum-Zinc Plated, Struktur Pulvermaling

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**