

MultipacPRO 19" Chassis Basic Kit

Such a kit enables a customer to configure the 3 different top / bottom covers.



CERTIFICERINGER



FUNKTIONER

For non-standardized assemblies (1 ... 5 U) and standardized assemblies (1, 2 U) conforming to IEC 60297-3-105

Frame consists of two lateral parts and front/rear panel

Material: aluminium

Select further components (Accessories)

SPECIFIKATIONER

Materiale:	Aluminium
Type:	Configurable
Produktfamilie:	MultipacPRO
EMC Shielding:	No (Retrofittable)
Product Type:	Subrack/Chassis

Table 1/1

Katalognummer	Rack Height	Dybde	Usable Width	Mounting	Complies With	Certificeringer
20860-202	1U	280mm	403mm	Rack	IEC 60297-3-100	RoHS

Katalognummer	Rack Height	Dybde	Usable Width	Mounting	Complies With	Certificeringer
20860-203	1U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-204	1U	400mm	403mm	Rack	IEC 60297-3-100	
20860-205	1U	460mm	403mm	Rack	IEC 60297-3-100	
20860-201	1U	220mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-210	2U	220mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-214	2U	460mm	403mm	Rack	IEC 60297-3-100	
20860-213	2U	400mm	403mm	Rack	IEC 60297-3-100	
20860-211	2U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-212	2U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-221	3U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-219	3U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-222	3U	460mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-220	3U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-228	4U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-229	4U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-231	4U	460mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-230	4U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-240	5U	460mm	403mm	Rack	IEC 60297-3-100	RoHS

YDERLIGERE PRODUKTOPLYSNINGER

Please order mounting plate, cover and base plates, handles, telescopic slides separately.

Dimensions h = clear mounting height = H-8.1 mm, b = clear mounting width = 403 mm.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE