

Outdoor Comline ECL Cabinet



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism ensuring operational continuity.

CERTIFICERINGER



FUNKTIONER

IP 55

Heat dissipation through natural convection

Single wall, lightweight aluminium cabinet

SPECIFIKATIONER

Materiale: Aluminium

Table 1/3

| Katalognummer | Product Type | Produktfamilie | Rack Height | Højde | Bredde | Dybde |
|---------------|-----------------|----------------|-------------|-------|--------|-------|
| 12349-003 | Outdoor Cabinet | Comline ECL | 18U | 900mm | 700mm | 600mm |
| 12349-001 | Outdoor Cabinet | Comline ECL | 12U | 600mm | 600mm | 500mm |
| 12349-010 | Outdoor Cabinet | Comline ECL | 18U | 900mm | 600mm | 500mm |

| Katalognummer | Product Type | Produktfamilie | Rack Height | Højde | Bredde | Dybde |
|---------------|-----------------|----------------|-------------|--------|--------|-------|
| 12349-011 | Outdoor Cabinet | Comline ECL | 18U | 900mm | 700mm | 600mm |
| 12349-009 | Outdoor Cabinet | Comline ECL | 12U | 600mm | 600mm | 500mm |
| 12349-004 | Outdoor Cabinet | Comline ECL | 25U | 1200mm | 700mm | 600mm |
| 12349-012 | Outdoor Cabinet | Comline ECL | 25U | 1200mm | 700mm | 600mm |
| 12349-002 | Outdoor Cabinet | Comline ECL | 18U | 900mm | 600mm | 500mm |

Table 2/3

| Katalognummer | Wall Type | Door Type | Access | Cooling | EMC Shielding | Complies With |
|---------------|---------------|-------------|--------|--------------------|---------------|---|
| 12349-003 | Single Walled | Single Door | Front | Natural Convection | No | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-001 | Single Walled | Single Door | Front | Natural Convection | No | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-010 | Single Walled | Single Door | Front | Natural Convection | No | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-011 | Single Walled | Single Door | Front | Natural Convection | No | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |

| Katalognummer | Wall Type | Door Type | Access | Cooling | EMC Shielding | Complies With |
|---------------|---------------|-------------|--------|--------------------|---------------|---|
| 12349-009 | Single Walled | Single Door | Front | Natural Convection | No | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-004 | Single Walled | Single Door | Front | Natural Convection | No | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-012 | Single Walled | Single Door | Front | Natural Convection | No | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-002 | Single Walled | Single Door | Front | Natural Convection | No | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |

Table 3/3

| Katalognummer | Pakke mængde | Finish |
|---------------|--------------|-----------------------|
| 12349-003 | 1 | Struktur Pulvermaling |
| 12349-001 | 1 | Struktur Pulvermaling |
| 12349-010 | 1 | Struktur Pulvermaling |
| 12349-011 | 1 | Struktur Pulvermaling |
| 12349-009 | 1 | Struktur Pulvermaling |
| 12349-004 | 1 | Struktur Pulvermaling |
| 12349-012 | 1 | Struktur Pulvermaling |
| 12349-002 | 1 | Struktur Pulvermaling |

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelser af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE