

Panhead Screw, Torx, Self-Securing



Pan head Torx screws with different metric threads and lengths. With optional features like GND earthing function or "precoated thread".

Panhead Screw, Torx, St, zinc plated, M2.5 x 6 (Partially coated thread to prevent the screw from loosening on its own due to vibrations).

CERTIFICERINGER



FUNKTIONER

Pan Head Screw with torx, self-locking

SPECIFIKATIONER

Type: Panhead Screw
Product Type: Screw
Materiale: Stål

Table 1/1

Katalognummer	Length	Finish	Pakke mængde	Thread Size	Works With
24560-159	6mm	Forzinket Stål	100	M2.5	Backplanes, Test Adapters
21500-039	9.3mm	Forzinket Stål	100	M2.5	Front Panels, Horizontal Rails, Type H, Horizontal Rails, Type R

YDERLIGERE PRODUKTOPLYSNINGER

Torque max. 0.2 Nm.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE