

# PropacPRO Complete Desktop Case, Shielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. The case includes EMC shielding as standard.

## CERTIFICERINGER



## FUNKTIONER

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Shielded

Ventilation slots in base plate

Rear panel with vent slots

IP 20 in accordance with IEC 60529

Conforms with DIN EN 62368-1

## SPECIFIKATIONER

<b>Static Load:</b>	25kg
<b>Product Type:</b>	Case
<b>Type:</b>	Case for 19" Components
<b>Produktfamilie:</b>	PropacPRO
<b>EMC Shielding:</b>	Yes

Table 1/3

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Usable Height	Usable Width
---------------	-------------	------------	-------	--------------	---------------	--------------

24576-122	6U	84HP	446mm	1	245.7mm	432mm
24576-105	3U	42HP	386mm	1	112.3mm	219mm
24576-102	3U	28HP	326mm	1	112.3mm	148mm
24576-110	3U	84HP	326mm	1	112.3mm	432mm
24576-111	3U	84HP	386mm	1	112.3mm	432mm
24576-121	6U	84HP	326mm	1	245.7mm	432mm
24576-104	3U	42HP	326mm	1	112.3mm	219mm
24576-106	3U	63HP	266mm	1	112.3mm	326mm
24576-109	3U	84HP	266mm	1	112.3mm	432mm
24576-112	3U	84HP	446mm	1	112.3mm	432mm
24576-113	3U	84HP	506mm	1	112.3mm	432mm
24576-103	3U	42HP	266mm	1	112.3mm	219mm
24576-107	3U	63HP	326mm	1	112.3mm	326mm
24576-101	3U	28HP	266mm	1	112.3mm	148mm
24576-108	3U	63HP	386mm	1	112.3mm	326mm

Table 2/3

Katalognummer	Front Frame Construction	Cooling Option	Complies With	Finish	Højde	Materiale
24576-122	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	289mm	Aluminium
24576-105	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-102	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-110	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-111	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-121	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	289mm	Aluminium
24576-104	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium

Katalognummer	Front Frame Construction	Cooling Option	Complies With	Finish	Højde	Materiale
24576-106	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-109	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-112	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-113	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-103	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-107	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-101	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-108	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium

Table 3/3

Katalognummer	Beskyttelsesgrad	Bredde
24576-122	IP20	470.3mm
24576-105	IP20	257mm
24576-102	IP20	185.9mm
24576-110	IP20	470.3mm
24576-111	IP20	470.3mm
24576-121	IP20	470.3mm
24576-104	IP20	257mm
24576-106	IP20	363.7mm
24576-109	IP20	470.3mm
24576-112	IP20	470.3mm
24576-113	IP20	470.3mm
24576-103	IP20	257mm
24576-107	IP20	363.7mm

Katalognummer	Beskyttelsesgrad	Bredde
24576-101	IP20	185.9mm
24576-108	IP20	363.7mm

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**